



Universal – 6" Display

Blue™ Easy Reader™ 4H/2C

Single Stage / Multi-Stage / Heat Pump

Non-Programmable or Selectable 7-Day Programmable Thermostat

Hardwired or Battery Powered with Power Stealing Assist

6-Square-Inch Display



1F95EZ-0671

Universal 4 Heat / 2 Cool

Super-Large Numbers and Letters

Easy-to-Use and Easy-to-Read

Intuitive Operating Choices

Simple One-Button,
One-Function Operation
means nothing to learn

Ships in Non-Programmable Mode

7-Day Programming mode available

Temperature Setpoint Limits

Dual Fuel Capable

with Smart Fuel™ Logic Program
(no outdoor sensor required)

5-Year Limited Warranty



1F95EZ-0671

Easy Reader – A Thermostat Unlike Any Other.

Designed Expressly for People Who Demand Easy-to-Read and Simple-to-Use Products....to Enhance Living!

The fastest-growing customer segment in history – Boomers – asked for a thermostat that is easier to read, easier to understand and easier to use. Blue™ Easy Reader thermostat offers display numbers and letters twice as large as most other thermostats, homeowner-friendly language and mode buttons with one-touch functionality for easy operation.

White-Rodgers™


EMERSON
Climate Technologies

Blue™ Easy Reader™ 4H/2C

6-Square-Inch Display
4 Heat / 2 Cool
Single Stage / Multi-Stage / Heat Pump

1F95EZ-0671

Programming

Installer configurable system applications
Choice of non-programmable or 7-day program (installer menu selectable)
2 time and 2 temperature settings per program (1 setback) heat and cool, or selectable 4 time and 4 temperature settings (2 setbacks)
Energy savings up to 30%
Patented pre-programmed schedule simplifies time and temperature programming

Display

Large, 6-square-inch display
Blue, lighted display for easier low-light viewing
Large, easy-to-read character size
Large “one-button one-function” keys for easy operation

Performance

Choice of battery-powered with optional power stealing assist or hardwired with battery backup
Dual Fuel capable with built-in Smart Fuel™ Logic Program (no outdoor sensor required)
Selectable Energy Management Recovery
Meets California Building Code, Title 24 Non PCT
Fast (FA) or slow (SL) heating cycle anticipation
Exclusive “Call for Service” diagnostic indicator
Compressor lockout protection
Millivolt compatible
Electric heat option
Intuitive menu-driven setup, programming and operation, with audio prompt to confirm entries

Comfort & Convenience

Permanent program retention during power loss
Indefinite setpoint Hold or temporary temperature override
Temporary temperature override – will override program for two hours
Heating and cooling, heating only or cooling only configuration (installer selectable)
Setpoint temperature “limited range” capable
Maintains room temperature to within +/- 1°F
Room temperature display can be recalibrated up to +/- 4°F

Terminal Designations* Terminal Block Wire Connections



*See installation instructions or www.white-roddgers.com for terminal descriptions

Contractor Branding

Imprint thermostat with your contact information. See your wholesaler or visit white-roddgers.com.

Thermal Specifications

Setpoint Temperature Range:
45° to 99° F (7° to 37° C)
Rated Differential:
Heat 0.6° F; Cool 1.2° F
Operating Ambient Temperature:
32° to 105° F (0° to 41° C)
Operating Humidity Range:
90% non-condensing maximum
Shipping Temperature Range:
-40° to 150° F (-40° to 66° C)

Electrical Specifications

Rating
Battery Power: mV to 30 VAC,
NEC Class II, 50/60 Hz or DC
Input Hardwire: 20 to 30 VAC
1.5 Amps (load per terminal)
2.5 Amps maximum load (all terminals combined)
Standard Systems
Single Stage gas, oil, electric
Single Stage heat pump
Millivolt systems
Multi-Stage gas, oil, electric
Multi-Stage heat pump

Dimensions

6.4" W x 4.2" H x 1.7" D

Accessories

Thermostat Guards
Clear – F29-0198
Metal – F29-0220 (solid base)
Wallplates
F61-2600 (8.1"W x 5.4"H)
F61-2634 (6.5"W x 5"H)

For Additional Information

Visit www.white-roddgers.com

Single Stage	Multi-Stage	Heat Pump	Programs	Applications			Power Source	Selectable Performance Features						Comfort and Convenience Features						
				Gas/Oil/Electric	3 Wire Zone	Millivolt		Auto Changeover	Programmable Fan	Energy Mgt. Recovery	Dual Fuel Option	Temperature Setpoint Limits	Indoor Remote Sensor	Outdoor Remote Sensor	Lighted Display*	Audible Feedback	Cool Savings™	Daylight Savings Adjustment	Ignition Module Reset	Permanent Memory
1/1	2/2	4/2	Ø, 7	✓	✓	✓	B,H,PA			✓	✓	✓			✓	✓		✓	✓	✓

B=Battery, H=Hardwired, PA=Power Stealing Assist * Optional Continuous Display Light w/Hardwire Connection

White-Rodgers™

Saint Louis, Missouri
314-553-3600

Markham, Ontario
905-948-3411

www.white-roddgers.com
www.emersonclimate.com

The Emerson logo is a trademark and a service mark of Emerson Electric Co.


EMERSON™
Climate Technologies

WR-3708-2