GoodmanElectronic Controls



Fast and Easy Direct OEM Replacement for Air Handler, Integrated Furnace and Outdoor Controls



Direct OEM Replacement ControlFast drop-in OEM mounting and wiring.



Source with other HVAC ControlsSave time by finding these boards at your local HVAC distributor.



System Diagnostics for Faster Servicing7 segment or flashing diagnostic LED aids in quicker and accurate system troubleshooting.



Complete Cross Reference Extensive and up-to-date cross reference by OEM model number.



Communicating SystemsControls to support legacy 24VAC or communicating system wiring.


Goodman ComfortNet™



50T35-743



50M56-707



50M56-743



Goodman Integrated Furnace Controls









Models	50T35-743	50A55-743	50M56-743	50M56-707	
Control Type	IFC Direct OEM Replacement Single Stage Systems PSC Blower Motor				
Blower Speeds	Heat, Cool	Heat, Cool	Lo Heat, Hi Heat, Cool	Heat, Cool	
Key Differentiator	9-pin Main Connector	7s Ignitor Warm-up	2-stage Gas Valve	17s Ignitor Warm-up	
Versatility	Replaces 9 Parts	Replaces 10 Parts	Replaces 9 Parts	Replaces 14 Parts	
Harness Included	Yes	_	_	_	
Diagnostics	System Diagnostic LED	System Diagnostic LED	System Diagnostic LED w/ Fault Recall	System Diagnostic LED w/ Fault Recall, Flame Test Pad	
Mounting	Drop-in Replacement	Drop-in Replacement	Drop-in Replacement	Drop-in Replacement	
Fuse	On Board	On Board	On Board	On Board	
lgnitor Voltage	120V	120V	120V	120V	
Dedicated Humidification (Optional)	120V or 24V	120V	120V	120V	
Electronic Air Cleaner (Optional)	120V	120V	120V	120V	
Heat-on-Delay	30s	30s	30s	30s	
Heat-off-Delay	90/120/150s	90/120/150/180s	100/150s	100/150s	
Cool-on-Delay	5s	5s	6s	6s	
Cool-off-Delay	60s	45s	45s	45s	

Goodman ComfortNet[™] Communicating Systems







Models	50C51-707	48C21-707		
Control Type	IFC Direct OEM Replacement Two-Stage, Variable Speed Blower Motor - Communicating or Legacy 24V Systems	Air Handler Direct OEM Replacement Two- Stage Electric Heat, Variable Speed Blower Motor - Communicating or Legacy 24V Systems		
Versatility	Replaces 13 Parts	Replaces 13 Parts		
Harness Included	_	_		
Diagnostics	7 Segment System Diagnostic LED	7 Segment System Diagnostic LED		
Mounting	Drop-in Replacement	Drop-in Replacement		
Fuse	On Board	On Board		
Ignitor Voltage	120V	_		
Dedicated Humidification (Optional)	120V	_		
Electronic Air Cleaner (Optional)	120V	_		
Heat-on-Delay	30s	Os (electric)		
Heat-off-Delay	90/120/150/180s	90s (electric)		
Cool-on-Delay	5s (legacy)	5s (legacy)		
Cool-off-Delay	45s (legacy)	60s (legacy)		

Model	49S25-707				
Control Type	AC or Heat Pump Direct OEM Replacement Two-Stage Compressor, PSC or ECM Outdoor Fan Motor - Communicating or Legacy 24V Systems				
Versatility	Replaces 11 Parts				
Harnesses Included	_				
Diagnostics	7 Segment System Diagnostic LED				
Mounting	Drop-in Replacement				
Fuse	On Board				
Compressor Short Cycle Delay	3min				
Compressor Minimum Run Time	30s				
Field Test Time	5s				
RV Shift Delay	0/5/15/30s (comm) 30s (legacy)				
Maximum Defrost Cycle Time	10min				
Compressor Run Time Until Defrost	30/60/90/120 min				
Outdoor Fan On/Off Delay	1s				

Cross Reference Information

Control Number	50M56-707	50A55-743	50T35-743	50M56-743	50C51-707	48C21-707	49525-707
		IC	М				
ICM280			Х				
ICM286		Х					
ICM2810	Χ						
		Good	man				
0130F00005		Х					
0130F00005S		Χ					
0130F00006				Х			
0130F00006S				Х			
B18099-06			Χ				
B18099-08			Χ				
B18099-13			Χ				
B1809913S			Χ				
PCB00109				Х			
PCBBF110		Х					
PCBBF110S		Х					
PCBBF112		Χ					
PCBBF122				Х			
PCBBF123		Х					
PCBBF132S				Χ			
PCBBF140S	Χ						
PCBBF140	Χ						
PCBBF138S	Χ						
PCBBF138	Χ						
PCBBF136S	Χ						

Control Number	50M56-707	50A55-743	50T35-743	50M56-743	50C51-707	48C21-707	49525-707
PCBBF136	Χ						
PCBBF135S	Х						
PCBBF135	Χ						
PCBBF134S	Χ						
PCBBF134	Χ						
PCBBF162				Χ			
PCBBF162S				Χ			
PCBGR102							Χ
PCBGR102S							Χ
PCBHR103							Χ
PCBHR103S							Χ
PCBHR104							Χ
PCBHR104S							Χ
PCBJA101						Х	
PCBJA101S						Χ	
PCBJA102						Х	
PCBJA102S						Χ	
PCBJA103						Χ	
PCBJA103S						Χ	
PCBJA104						Χ	
PCBJA104S						Х	
PCBKF101S					Χ		
PCBKF102					Χ		
PCBKF102S					Χ		
PCBKF103					Χ		
PCBKF105S					Χ		

Control Number	50M56-707	50A55-743	50T35-743	50M56-743	50C51-707	48C21-707	49525-707
		Tra	ne				
CNT04664			Χ				
	W	nite-F	Rodge	ers			
48C21-289						Х	
48C21-707						Х	
48C21-290-01						Х	
48C21-290-02						Х	
48C21-290-04						Х	
49C25-289-01							Х
49J22-289							Χ
49J22-289-02							Χ
49K25-289-01							Χ
49S25-707							Χ
50A55-289		Χ					
50A55-743		Χ					
50C51-289-01					Х		
50C51-289-02					Х		
50C51-289-90					Х		
50C51-290					Х		
50C51-290-01					Х		
50C51-290-02					Х		
50C51-290-03					Х		
50C51-707					Х		
50M56-289				Χ			
50M56-290				Χ			
50M56-707	Х						
50M56-743				Х			
50T55-289		Χ					
50M56-291	Х						
50M56-281	Х						
50T35-730			Χ				
50T35-730-1			Χ				
50T35-743			Χ				

THE WHITE-RODGERS MOBILE APP:

Answers at your fingertips, with your smartphone or tablet.

- √ Latest cross reference
- ✓ Installation instructions
- ✓ Spec sheets
- ✓ Product selection









R-4610-2 (8/20)

©2020 Emerson Electric Co. • White-Rodgers and Emerson are trademarks of Emerson Electric Co. All rights reserved • Customer Service or Technical Help: 888-725-9797 • Emerson.com/White-Rodgers