## 36C03 (U) -333 and -433 Universal Combination Controls Cross Reference Chart

	Part Number	Comments	
Robertshaw 7	36C03-333		
1	700-101	Regulator of replacement is set at 3.5 W.C.; requires use of reducer bushings (included)	
Robertshaw 7	700-102	Replacement requires use of reducer bushings (included)	
Robertshaw 7	700-402		
Robertshaw 7	700-419	May require use of reducer bushings (included) and LP conversion kit (F92-0737)	
Robertshaw 7	720-402	Replacement has no side outlet and has 1/2" inlet and 3/4" outlet	
Honeywell \	V800A 1070		
Honeywell \	V800A 1484	Order F92-0737 regulated LP kit to achieve 11.0 regulation of replacement	
Honeywell \	VR8300A 3500		
36C0	03-433		
Robertshaw 7	700-105	Regulator of replacement is set at 3.5 W.C.; may require use of reducer bushings (included)	
Robertshaw 7	700-106	Replacement may require use of reducer bushings (included)	
Robertshaw 7	700-185	Regulator of replacement is set at 3.5 W.C.; may require use of reducer bushings (included)	
Robertshaw 7	700-401	Regulator of replacement is set at 3.5 W.C.; may require use of reducer bushings (included); no side taps	
Robertshaw 7	700-404	Replacement may require use of reducer bushings (included); no side taps	
Robertshaw 7	700-405	Regulator of replacement is set at 3.5 W.C.	
Robertshaw 7	700-407	Regulator of replacement is set at 3.5 W.C.; may require use of reducer bushings (included); no side taps	
Robertshaw 7	700-411	Replacement requires use of LP conversion kit (F92-0737); may require use of reducer bushings (included); no side taps	
Robertshaw 7	700-412	Replacement may require use of reducer bushings (included) and LP conversion kit (F92-0737); no side taps	
	720-404	36C03-433 uses HO6E-36 thermocouple	
Honeywell \	V800A 1088		
Honeywell \	V800A 1492	Order F92-0737 regulated LP kit to achieve 11.0 regulation of replacement	
	VR8300A 3518	36C03-433 uses HO6E-36 thermocouple	
Honeywell \	VR8300A 4508		
Honeywell \	VR8300A 4516	36C03-433 uses HO6E-36 thermocouple	
Honeywell \	VR8300M 4505		
36C03U-333			
Honeywell \	VS820A 1336		
	VS820A 1047		
	700-502	36C03U-333 has 1/2" inlet and 3/4" outlet	
	700-504		
Robertshaw 7	700-503	Install F92-0737 kit to achieve non-regulated setting	
36C03U-433			
Robertshaw 7	700-506	36C03U-400 is also available, 36C03U-400 has no LP kit or bushings	
	700-511	Replacement valid for vented applications only	
	700-512	Replacement valid for vented applications only	
	700-515	Requires use of LP kit (included), replacement valid for vented applications only	
	VS800A-1054	, , , , , , , , , , , , , , , , , , , ,	
	VS800A-1336		
	VS800A-1054		
	VS800A-1336		