

90-T40F3

90-T SERIES ENERGY LIMITING 24 VAC TRANSFORMERS

For industrial, heating and air conditioning controls applications.

FEATURES

- · Color coded primary leads
- Color coded secondary leads
- Multi-mount styles available

SPECIFICATIONS

UR/CUR File Number E507466

90-T SERIES INHERENTLY LIMITED 24 VAC TRANSFORMERS - MULTI-MOUNT WITH PLATE (CLOSED CONSTRUCTION)

PRIMARY	SEC.	VA	HZ	PRIMARY / SEC. CONNECTIONS	MARS PART NO.	JARD PART NO.	MODEL NUMBER	ITEM NUMBER
120 VAC	24 VAC	40	60	Leads / Leads	50302	4011M	90-T40M1	90-T40M1
208 / 240 VAC	24 VAC	40	50/60	Leads / Leads	50303	4021M	90-T40M2	90-T40M2
120 / 208 / 240 VAC	24 VAC	40	60	Leads / Leads	50304	4031M	90-T40M3	90-T40M3

90-T SERIES NOT INHERENTLY LIMITED 24 VAC TRANSFORMERS - MULTI-MOUNT WITH PLATE (CLOSED CONSTRUCTION)

PRIMARY	SEC.	VA	HZ	PRIMARY / SEC. CONNECTIONS	MARS PART NO.	JARD PART NO.	MODEL NUMBER	ITEM NUMBER
120 / 208 / 240 VAC	24 VAC	50	60	Leads / Leads	50314	5031M	90-T50M3	90-T50M3

90-T SERIES INHERENTLY LIMITED 24 VAC TRANSFORMERS - FOOT-MOUNT (OPEN CONSTRUCTION)

PRIMARY	SEC.	VA	HZ	PRIMARY / SEC. CONNECTIONS	MARS PART NO.	JARD PART NO.	MODEL NUMBER	ITEM NUMBER
120 VAC	24 VAC	40	50/60	Leads / Leads	50352	4011F	90-T40F1	90-T40F1
208 / 240 VAC	24 VAC	40	50/60	Leads / Leads	50353	4021F	90-T40F2	90-T40F2
120 / 208 / 240 VAC	24 VAC	40	50/60	Leads / Leads	50354	4031F	90-T40F3	90-T40F3

90-T SERIES NOT INHERENTLY LIMITED 24 VAC TRANSFORMERS - FOOT-MOUNT (OPEN CONSTRUCTION)

PRIMARY	SEC.	VA	HZ	PRIMARY / SEC. CONNECTIONS	MARS PART NO.	JARD PART NO.	MODEL NUMBER	ITEM NUMBER
120 / 208 / 240 VAC	24 VAC	50	50/60	Leads / Leads	50308	5031F	90-T50F3	90-T50F3

90-T SERIES NOT INHERENTLY LIMITED 24 VAC TRANSFORMERS - FOOT-MOUNT (MANUAL RESET, OPEN CONSTRUCTION)

PRIMARY	SEC.	VA	HZ	PRIMARY / SEC. CONNECTIONS	MARS PART NO.	JARD PART NO.	MODEL NUMBER	ITEM NUMBER
120 / 208 / 240 VAC	24 VAC	50	50/60	Leads / Leads	50327	5041C	90-T50C3	90-T50C3
120 / 208 / 240 VAC	24 VAC	60	50/60	Leads / Leads	50327	6041C	90-T60C3	90-T60C3
120 / 208 / 240 VAC	24 VAC	75	50/60	Leads / Leads	50321	7541C	90-T75C3	90-T75C3
120 / 208 / 240 / 480	24 VAC	100	50/60	Leads / Leads	50540	10041C	90-T100C4	90-T100C4