






Emerson™ system protectors solution



Choose Emerson. Install confidence.

When it comes to the refrigeration systems you install and maintain, what matters the most? It's keeping them running at peak efficiency. Keeping your reputation intact and your customers satisfied. It's the kind of protection you can only get from the established industry leader, Emerson Climate Technologies. Our EK filter driers, HMI hermetic moisture indicators, along with many other high performance products, provide you with a total package that delivers more reliable and longer lasting protection from moisture and contaminants. Come see for yourself what the total package is all about.

Product	Application	Feature
 <p>Liquid line filter drier (EK)</p>	<ul style="list-style-type: none"> • Compacted bead filter drier that provides long-lasting protection from moisture and contaminants • Premium universal replacement for CFC, HCFC and HFC 	<ul style="list-style-type: none"> • High moisture and acid removal capacity • Optimized to use with HFC refrigerants and POE lubricants • 680 psig maximum working pressure • 20 micron outlet pad for maximum filtration
 <p>Steel liquid and suction filter drier (STAS)</p>	<ul style="list-style-type: none"> • Replaceable core filter drier for CFC, HCFC and HFC refrigerants • Ideal for use in large commercial air conditioning and refrigeration systems 	<ul style="list-style-type: none"> • Slotted cover/unique internal hardware for ease of installation • Full flow fittings for low pressure drop • R-410A rated models available
 <p>Brass take-apart suction line filter drier (BTAS)</p>	<ul style="list-style-type: none"> • Replaceable core filter drier for suction line service • Ideal for commercial refrigeration applications 	<ul style="list-style-type: none"> • Corrosion resistant brass body with stainless steel bolts • Full flow fittings for low pressure drop • Filter and filter drier cartridges available
 <p>Filter drier cores and filters</p>	<ul style="list-style-type: none"> • Universal replacement cores and filter cores to remove moisture, acid, and debris from the system • For use in Emerson shells and other take-a-part type filter drier shells 	<ul style="list-style-type: none"> • Water capacities to suit specific system conditions • Exceptional acid capacities for normal system protection, or to clean up after a compressor burnout • Activated carbon blend for soluble contaminant and wax removal (W-HH Series)
 <p>Hermetic moisture indicators (HMI)</p>	<ul style="list-style-type: none"> • A unique high accuracy moisture indicator for CFC, HCFC, and HFC refrigerants • Designed to accurately determine the moisture content of a system's refrigerant 	<ul style="list-style-type: none"> • Highest sensitivity moisture indicator available provides best protection • Hermetic, leak-free construction eliminates leaks and refrigerant loss • Single indicator for all common refrigerants • Wide angle viewing/high visibility window for easy monitoring