Copeland Outdoor Refrigeration Unit X-Line

Now available in 460V for medium temperature applications

The Copeland outdoor refrigeration unit, X-Line Series, is now offering a 460V option for 4.5-6 HP medium temperature applications in food retail. This new offering has the same benefits of our other fixed speed X-Line units.

The Copeland outdoor refrigeration unit was designed based on three factors:

Energy efficiency

Scroll compressor technology, variable speed fan motors, large capacity condenser coils, and advanced control algorithms work together to significantly reduce energy consumption. These new units also comply with the Department of Energy's Annual Walk-In Energy Factor (AWEF) standards.

Reliability

Equipment reliability is greatly enhanced by combining the proven reliability of Copeland scroll compressors with advanced Copeland compressor electronics technology. Each unit has built-in diagnostics and protection that can alert and record alarms independently or communicate with building management systems.

Flexibility

The ultra-quiet variable speed fan motor significantly reduces exterior sound levels and is combined with a lightweight weather-resistant cabinet, slim footprint, and optional wall mounting capability to deliver unmatched installation.





Standard features

- Pre-painted enclosures for corrosion protection
- Electronic defrost control with programmable defrost scheduling
- Brass service valves located externally for easy access
- Electronic low-pressure control for quick setup and higher accuracy
- Receivers with pressure relief valve, liquid shut- off valve and charging port
- · Easy to read moisture indicator
- Variable-speed PSC fan motors

Capacity and efficiency

- · Advanced compressor electronics diagnostics
- Over-sized condenser coils with additional fin corrosion protection for coastal zones
- Lightweight, slim-line profile for maneuverability and ease of installation

- All units are factory tested for braze joint leaks, wiring connections, electrical continuity and start-up performance
- Heated insulated receiver for low-ambient operation



	Medium Temp Capacity @ 95°F Ambient / 25°F Evap														
Unit	Comp.	R-134a		R-404A		R-407A		R-407C		R-448A		R-449A		R-507	
		Cap.	AWEF	Cap.	AWEF										
XFAM- 045Z	ZS33KAE	25500	-	39300	7.6	36600	7.6	35200	-	37400	7.6	37400	7.6	41400	-
XFAM- 050Z	ZS38K4E	29300	-	44700	7.6	43200	7.6	42500	-	44000	7.6	44000	7.6	46400	-
XFAM- 060Z	S45K4E	34600	-	51000	7.6	51000	7.6	49900	-	50000	7.6	51000	7.6	54000	_

This refrigeration system is designed and certified for use in walk-in cooler applications. See Copeland.com/CopelandOPI for complete specifications.

To place an order, select:					Base N	/lodel	Electr	ical						
	х	F	А	М	-	0	4	5	z	-	т	F	D	
Family = X-Line F = Multiple Refrigerant A = Air Cooled M = Medium Temp							050 = 060 =	= 1/2 HP = 5 HP = 6 HP Scroll			TFD = 460V 3ph-60Hz			



Scan for more information or visit copeland.com/CopelandOutdoorUnit

COPELAND

2021ECT-17 R1 (8/21) ©2024 Copeland LP.