

The ACC is a charge compensator that is designed to work in heat pump applications. It increases system efficiency by storing extra refrigerant in the heating mode. It then returns refrigerant back into circulation in the cooling mode.

**R-410A**



### Features

- Solid copper connection
- Corrosion resistant epoxy powder paint finish

### Nomenclature example: ACC-3637S

| ACC    | 36                        | 3              | 7                          | S   |
|--------|---------------------------|----------------|----------------------------|-----|
| Series | Internal Volume (cu. in.) | Diameter (in.) | Connection Size (in. 1/8") | ODF |

### Specifications

- Maximum working pressure: 680 psig
- UL/CUL file number: SA5760

### Ordering Information

| PCN    | Description | Internal Volume (cu. in.) | Liquid Line Connection | Connection | Dimensions (in.) |       |      | Holding Capacity (oz.) |       |
|--------|-------------|---------------------------|------------------------|------------|------------------|-------|------|------------------------|-------|
|        |             |                           |                        |            | A                | B     | C    | R-410A                 |       |
|        |             |                           |                        |            |                  |       |      | 75°F                   | 125°F |
| 066631 | ACC-2336S   | 23                        | 3/8 ODF                | 3/4 ODF    | 7.19             | 3.33  | 3.50 | 15                     | 13    |
| 066632 | ACC-3636S   | 36                        | 3/8 ODF                | 3/4 ODF    | 8.94             | 5.08  | 3.50 | 24                     | 20    |
| 066633 | ACC-3637S   |                           | 3/8 ODF                | 7/8 ODF    | 8.94             | 5.08  | 3.50 | 24                     | 20    |
| 066634 | ACC-4736S   | 47                        | 3/8 ODF                | 3/4 ODF    | 10.18            | 6.32  | 3.50 | 31                     | 26    |
| 066635 | ACC-4737S   |                           | 3/8 ODF                | 7/8 ODF    | 10.18            | 6.32  | 3.50 | 30                     | 25    |
| 066493 | ACC-6236S   | 62                        | 3/8 ODF                | 3/4 ODF    | 12.06            | 8.20  | 3.50 | 40                     | 34    |
| 066636 | ACC-6237S   |                           | 3/8 ODF                | 7/8 ODF    | 12.06            | 8.20  | 3.50 | 40                     | 33    |
| 066637 | ACC-7837S   | 78                        | 3/8 ODF                | 7/8 ODF    | 14.11            | 10.25 | 3.50 | 51                     | 43    |
| 066638 | ACC-7836S   |                           | 3/8 ODF                | 3/4 ODF    | 14.11            | 10.25 | 3.50 | 50                     | 42    |
| 066639 | ACC-9536S   | 95                        | 3/8 ODF                | 3/4 ODF    | 15.86            | 12.00 | 3.50 | 60                     | 51    |
| 066640 | ACC-9537S   |                           | 3/8 ODF                | 7/8 ODF    | 15.86            | 12.00 | 3.50 | 59                     | 50    |

### Dimensional Data

