# MRLDS-250 Infrared Refrigerant Gas Detector

The Modular Refrigeration Leak Detection Sensor is Emerson's state-of-the-art infrared refrigerant gas detector which can detect a wide range of gases. The MRLDS can be used on a stand-alone basis or integrated into a supervisory controller. The MRLDS-250 can be used in locations that require continuous monitoring and to add gas detection solutions to an existing system.

## Broadband vs Gas Specific

The MRLDS-250 is available in two versions:

- The broadband gas detector is used as a general purpose gross leak detector and is factory tested and certified to +/- 35% accuracy.
- The gas specific version comes factory certified and calibrated with +/- 3% accuracy to the target refrigerant when there is a need for more accurate detection.

### Benefits

- Refrigerant monitoring can reduce energy consumption and keep equipment cooling properly.
- The MRLDS-250 can pay for itself by reducing the amount of refrigerant being lost when used in a continuous monitoring program.
- MRLDS-250 is immune to cross sensitivities to combustible and toxic gas as well as changes in temperature and humidity.
- Protect people, products, and equipment from dangerous situations and costly failures
- IR sensing technology allows for low-level leak detections (0-3,500ppm), delivering up to 5-7 years of maintenance-free operation without the need for costly annual gas calibrations.
- Simple to use interface gives the ability to set all parameters and outputs without opening the unit, moving jumpers, using multimeters or adjusting potentiometers.




#### Features

- Detects all refrigerants (CFC, HFC's, HCFC, HFO's) including HFO1234YF, HFO1234ZE, R410a & R22
- Bright alpha-numeric LED real-time display
- On-board LED indicator and audible alarm to alert personnel in the area that levels have exceeded the desired limit
- Can connect to any controller through analog output on-board or Modbus RTU interface
- No field calibrations required
- Maintenance mode to avoid false alarms during maintenance
- Scalable 0-3500ppm detection range
- Onboard relay NO, NC: can be programed to be failsafe (normally energized)



## Specifications


	Specification	Description
	Power Supply	24 VDC, 24 VAC 50/60 Hz, 2.5 W max
	Power Monitoring	Green LED
	Visual Alarm	Red 4-digit LED display
	Audible Alarm	Buzzer (audible alarm), enable/disable (Default enabled)
	Fault Monitoring	Fault codes presented to user
	Analog Outputs	4-20 mA; 0-5 V; 0-10 V; 1-5 V; 2-10 V (Default 1-5V)
	Relay	1 relay rated 1 A @ 24 VAC/VDC (0.5A, 125V AC UL rating)
	Range	0-3500 ppm
	Squelch1	Readings below 75 ppm are squelched by default
	Communication	Modbus RTU over RS-485 Baud rate: 9,600 or 19,200 (selectable)
	Alarm Delay	Selectable; 0 to 15 minutes
	Response Time, T90	5 minutes
	Temperature Rating	-22° to 104° F (-30° to 40° C)
	Humidity and Elevation	5-90% RH, non-condensing, 0-10,000 ft. altitude
	IP Rating	Not IP rated. An accessory splash guard is available for areas requiring additional protection from wash down.
	Dimensions	4.0" x 5.5" x 1.5", 102 x 140 x 37 mm
	Weight	6.3 oz, 180 g
	Approvals	CE, MET/IEC/EN 61010-1



Broadband Gas Groups 1-4

## Order Information

Part #	Description
809-0030	MRLDS-250, Broadband
809-0031	MRLDS-250, Calibrated to R-22
809-0034	MRLDS-250, Calibrated to R-404A
809-0035	MRLDS-250, Calibrated to R-407A
809-0040	MRLDS-250, Calibrated to R-422D
809-0041	MRLDS-250, Calibrated to R-448A
809-0042	MRLDS-250, Calibrated to R-449A
809-0043	MRLDS-250, Calibrated to R-513A
809-0044	MRLDS-250, Calibrated to R-507
603-1100	MRLDS Splash Guard Mounting Kit



Gas-Specific MRLDS-250 Gas Detectors

2018RS-14 R1 (6/18) Emerson is a trademark of Emerson Electric Co. ©2018 Emerson Climate Technologies, Inc. All rights reserved.

## EMERSON. CONSIDER IT SOLVED.