

Features

- Compact designs
- Coil windings are insulated to provide shock and vibration protection
- ASC2 is designed to provide weather protection
- Interchangeable housings

Voltage Options

- 24V 50/60 Hz
- 120V 50/60 Hz (standard)
- 208-220/208-240V 50/60 Hz
- 480V 50/60 Hz
- 120-240V 50/60 Hz
- 12V D.C. (MM Series recommended)
- 24V D.C. (MM Series recommended)

ASC2 – DIN



Requires ASC2 female connector (PCN 059261).

MMG – Special DC



Nomenclature

Coil Code		
A	M	G
Series	Insulation	Enclosure
A = 12 Watt B = 15 Watt C = 18 Watt D = 7 Watt M = 4 Watt	B or G = Class B M = Class F H = Class H	C = Conduit Connection F = Open Frame Leads G = Junction Box L = Grommet 18" Leads S = Spade Connection

AMC - 1/2" Conduit



AMG - Junction Box



AMS - Open Frame



MAGMAX Coil (Type MM): For Use On DC Applications Only

Voltage	Amperes Holding	Watts Holding
12VDC	0.4	4
24VDC	0.4	4

Solenoid Coil Prefix Selection Table

Valve Type	J-Box	Conduit	Leads	Spades	Molded-DIN With Connector
50RB	-	-	SML*	-	-
100RB	AMG	AMC	AMF	AMS	ASC2
200RB / 200RD	AMG	AMC	AMF	AMS	ASC2
222CB (Steam)	AHG	AHC	-	-	-
500RB	DMG	-	DMF	DMS	-
540RA	-	-	-	DMS	ASC2
222CB (Water)	AMG	AMC	AMF	AMS	ASC2
Special DC Application	MMG	-	MMF	-	-

* SML is OEM - RMF is Wholesale replacement

Note - All coils NEMA1 except ASC2 NEMA2

AM/EM Coil:

- 204CD
- 214CB
- 211CA
- 222CB
- 210CA

Nominal Voltage and Frequency	Applied Voltage and Frequency	204CD		214C		211CA		222CB		210CA	
		Inrush	Holding	Inrush	Holding	Inrush	Holding	Inrush	Holding	Inrush	Holding
24/60	24/60	1.23	0.61	1.17	0.61	0.92	0.61	1.00	0.74	0.92	0.61
120/60	120/60	0.23	0.14	0.22	0.14	0.17	0.14	0.19	0.16	0.17	0.14
240/60	240/60	0.13	0.08	0.12	0.08	0.10	0.08	0.11	0.08	0.10	0.08
480/60	480/60	0.06	0.04	0.05	0.04	0.05	0.04	0.05	0.04	0.05	0.04

See the MM (MAGMAX) Series Coil for DC Applications

AM Coil: 702RA

Nominal Voltage and Frequency	Applied Voltage and Frequency	Amperes		VA Holding	Watts Max.	Coil Insulation
		Inrush	Holding			
24-50/60	24/50	1.70	1.00	24	17/12	Class F Molded
24-50/60	24/60	1.41	0.64	15		
120-50/60	120/50	0.38	0.24	29		
120-50/60	120/60	0.32	0.16	19		
208-220/50 208-240/60	208/50	0.17	0.10	21		
208-220/50 208-240/60	208/60	0.15	0.06	13		
208-220/50 208-240/60	220/50	0.20	0.14	33		
208-220/50 208-240/60	240/60	0.22	0.09	22		
480-50/60	480/50	0.10	0.07	33		
480-50/60	480/60	0.09	0.04	22		

See the MM (MAGMAX) Series Coil for DC Applications

AM Coil: 100RB 240RA 710/713RA

Nominal Voltage and Frequency	Applied Voltage and Frequency	Amperes		VA Holding	Watts Max.	Coil Insulation
		Inrush	Holding			
24-50/60	24/50	1.20	.96	23	17/12	Class F Molded
24-50/60	24/60	1.0	.74	18		
120-50/60	120/50	.25	.21	25		
120-50/60	120/60	.19	.16	19		
208-220/50 208-240/60	208/50	.14	.08	17		
208-220/50 208-240/60	208/60	.12	.06	12		
208-220/50 208-240/60	220/50	.16	.10	24		
208-220/50 208-240/60	240/60	.13	.08	19		
480-50/60	480/50	.06	.05	24		
480-50/60	480/60	.05	.04	19		

See the MM (MAGMAX) Series Coil for DC Applications

AM Coil: 200RB/200RD

Nominal Voltage and Frequency	Applied Voltage and Frequency	Amperes		VA Holding	Watts Max.	Coil Insulation
		Inrush	Holding			
24-50/60	24/50	2.00	.96	23	17/12	Class F Molded
24-50/60	24/60	1.6	.74	18		
120-50/60	120/50	.45	.21	25		
120-50/60	120/60	.36	.16	19		
208-220/50 208-240/60	208/50	.19	.08	17		
208-220/50 208-240/60	208/60	.15	.06	12		
208-220/50 208-240/60	220/50	.24	.10	24		
208-220/50 208-240/60	240/60	.19	.08	19		
480-50/60	480/50	.11	.05	24		
480-50/60	480/60	.09	.04	19		

See the MM (MAGMAX) Series Coil for DC Applications

**ASC2 Coil:
200RB/200RD
540RA**

Nominal Voltage and Frequency	Applied Voltage and Frequency	Amperes		VA Holding	Watts Max.	Coil Insulation
		Inrush	Holding			
24-50/60	24/50	2.18	1.07	26	15/12	Class H Molded
24-50/60	24/60	1.90	.81	19		
120-50/60	120/50	.43	.21	25		
120-50/60	120/60	.38	.16	19		
240-50/60	240/50	.24	.12	30		
240-50/60	240/60	.21	.09	22		

**DM Coil:
500RB**

Nominal Voltage and Frequency	Applied Voltage and Frequency	Amperes		VA Holding	Watts Max.	Coil Insulation
		Inrush	Holding			
24-50/60	24/50	1.80	.71	17	17/12	Class F Molded
24-50/60	24/60	1.56	.52	12		
120-50/60	120/50	.36	.14	17		
120-50/60	120/60	.31	.10	12		
240-50/60	240/50	.19	.08	19		
240-50/60	240/60	.17	.06	14		

**ASC2 Coil:
100RB
240RA
710/713RA**

Nominal Voltage and Frequency	Applied Voltage and Frequency	Amperes		VA Holding	Watts Max.	Coil Insulation
		Inrush	Holding			
24-50/60	24/50	1.67	1.10	26	15/12	Class H Molded
24-50/60	24/60	1.41	.83	20		
120-50/60	120/50	.31	.22	26		
120-50/60	120/60	.26	.16	20		
240-50/60	240/50	.17	.13	31		
240-50/60	240/60	.15	.10	23		

**DM Coil:
100RB
240RA
710/713RA**

Nominal Voltage and Frequency	Applied Voltage and Frequency	Amperes		VA Holding	Watts Max.	Coil Insulation
		Inrush	Holding			
24-50/60	24/50	1.21	.72	17	17/12	Class F Molded
24-50/60	24/60	1.02	.52	13		
120-50/60	120/50	.24	.14	17		
120-50/60	120/60	.20	.10	12		
240-50/60	240/50	.13	.08	20		
240-50/60	240/60	.11	.06	14		

**RMS/RMF Coil:
50RB**

Nominal Voltage and Frequency	Applied Voltage and Frequency	Amperes		VA Holding	Watts Max.	Coil Insulation
		Inrush	Holding			
24-50/60	24/50	.87	.50	12	RMF/7 RMS/10	Class F Molded
24-50/60	24/60	.90	.40	10		
120-50/60	120/50	.19	.19	22		
120-50/60	120/60	.17	.09	10		
208-50/60	208/60	.08	.03	7		
220-50/60	220/50	.10	.05	11		
240-50/60	240/50	.11	.06	14		
240-50/60	240/60	.10	.04	11		

Ordering Information

AMG Junction Box



6" Leads

AMC - 1/2" Conduit



18" Leads

AMS - Open Frame



18" Leads or
1.4" Spades

Voltage / Frequency	Description	PCN	Description	PCN	Description	PCN
24V 50/60 Hz	AHG 24V 50/60 Hz	057669	AMC 24V 50/60 Hz	057631	AMF 24V 50/60 Hz	057539
	AMG 24V 50/60 Hz	057341	AHC 24V 50/60 Hz	057736	AMF 24V 50/60 Hz	057538
	--	--	--	--	DMS 24V 50/60 Hz	062013
	DMG 24V 50/60 Hz	055129	--	--	RMF 24V 50/60 Hz	065677
	--	--	--	--	AMS 24V 50/60 Hz	057603
120V 50/60 Hz	AHG 120V 50/60 Hz	057673	AMC 120V 50/60 Hz	057598	RMF 120V 50/60 Hz	065678
	AMG 120V 50/60 Hz	057331	AHC 120V 50/60 Hz	057743	AMS 120V 50/60 Hz	057349
	DMG 120V 50-60 Hz	054762	--	--	RMS 120V 50/60 Hz	065204
208-220/208-240 50/60 Hz	AHG 208-220/208-240 50/60 Hz	057671	--	--	AMF 208-220/208-240 50/60 Hz	057540
	AMG 208-220/208-240 50/60 Hz	057342	AMC 208-220/208-240 50/60 Hz	057594	RMF 208-220/208-240 50/60 Hz	065679
	DMG 208-220/208-240 50/60 Hz	054764	--	--	AMS 208-220/208-240 50/60 Hz	057531
	--	--	--	--	RMS 208-220/208-240 50/60 Hz	065681
480V 50/60 Hz	AMG 480V 50/60 Hz	057527	--	--	AMF 480V 50/60 Hz	057534
120-240V 50/60 Hz	AMG 120-240V 50/60 Hz	057343	AMC 120-240V 50/60 Hz	057730	AMF 120-240V 50/60 Hz	062410
277V 60 Hz	AMG 277V 60 Hz	057528	--	--	AMF 277V 50/60 Hz	057533
	--	--	--	--	AMS 277V 50/60 Hz	057714
12V DC	AMG 12V DC	057521	AMC 12V DC	057596	--	--
24V DC	AMG 24V DC	057523	AMC 24V DC	057633	--	--

ASC2 – DIN



MMG




RMF



Voltage/Frequency	Description	PCN	Description	PCN
24V 50/60 Hz	ASC2 24/50-60	062792	--	--
24V 50/60 Hz	ASC2L 24/50-60	063542	--	--
120V 50/60 Hz	ASC2 120/50-60	062462	--	--
120V 50/60 Hz	ASC2 GS-2562-1	015384	--	--
208-220/208-240 50-60 Hz	ASC2 208-240/50-60	062463	--	--
208-220/208-240 50-60 Hz	ASC2 GS-2562-2	015383	--	--
12V DC	--	--	MMG 12V DC	063524
12V DC	--	--	MMF 12V DC	062972
24V DC	ASC2 24V DC	064375	MMG 24V DC	063526

Dual Voltage Wiring Diagram



A	B
120	240
240	480

AM and ASC 2 style DC coils should not be used for direct replacements on OEM equipment. The use of this coil on new applications may result in the valve not opening. New applications should use the MM coil because of the significant increase in opening power of the MM Coil over the standard AM and ASC 2 style DC coil.

Coil Enclosure Options

Options	Code
Junction Box	G
Conduit - 18" Leads	C
Open Frame - 18" Leads	F
Open Frame - Spades	S