

Sensi Touch 2 smart thermostat

The Sensi Touch 2 smart thermostat is the next evolution of smart thermostats by Copeland. With a new modern design, glass LCD touchscreen, enhanced user experience and compatibility with room sensors, this thermostat proves why Sensi smart thermostats are top rated by consumers.



1F96U-42WF White

1F96U-42WFB Black



WORKS WITH ROOM SENSORS

When paired with a Sensi room sensor, the Sensi Touch 2 smart thermostat can help reduce hot and cold spots by prioritizing or balancing temperatures where homeowners need it most.

BATTERY LIFE Up to 2 years

TOP-RATED DESIGN

A full color, glass touchscreen packaged in the industry's thinnest smart thermostat.

EASY TO INSTALL AND CONNECT

Easy-to-use app guides you through each step of the install for easy setup. Works with HVAC equipment found in most homes. Common wire (c-wire) is required.

CONTROL FROM ANYWHERE

The Sensi mobile app for iOS and Android give you total on-the-go access to adjust your thermostat from anywhere, anytime.

SMART HOME COMPATIBLE

Works with Amazon Alexa, Google Assistant and Samsung SmartThings smart home platforms.



PRIVACY PROTECTION

Sensi doesn't sell your personal information to third parties or use your thermostat activity data for other targeting/advertising purposes¹.

SMART MAINTENANCE

Homeowners can monitor the performance of their HVAC system with alerts and service reminders.

ENERGY SAVINGS

Save about 23% on HVAC energy² through features like flexible scheduling, remote access and usage reports.

ACCESSORY TERMINALS


Designated terminals for humidity control.

HEAT PUMP SETTINGS

Heat pump setting include temp. set points for both balance point and auxiliary lockout.

¹ PRIVACY PROTECTION: For full details, review the Sensi Privacy Policy at <https://sensi.copeland.com/en-us/legal>. Note: if you sign up for a program with a third party, such as a utility or controller, details and terms for that program are between you and the third party, not Copeland, and may include additional data collection. Certain add-on services require additional data to operate as intended. These services are not required and are optional.

² ENERGY SAVINGS: Calculated by comparing operation time for a nationwide sample of Sensi users with temperature adjustments averaging 4° in comparison to users with no adjustments. Savings vary based on equipment type/condition, insulation, climate & temperature adjustment size/frequency.



CONTRACTOR BRANDING

Put your name front and center on Sensi smart thermostats and in the Sensi app to stay top of mind and build lasting customer relationships. Scan the QR code to learn more.



Sensi Touch 2 smart thermostat

SPECIFICATIONS



ELECTRICAL RATING

20 to 30 VAC, 50/60 Hz
1.5 Amps maximum per terminal
2.5 Amps maximum (all terminals combined)

STANDARD SYSTEMS

Single-stage gas, oil, electric
Single-stage heat pump
Multi-stage gas, oil, electric
Multi-stage heat pump

SETPOINT RANGE

45°F to 99°F (7°C to 37°C)

ACCESSORIES

Wallplate: (white) SA6W (6.75" x 4.50")
Wallplate: (black) SA6B (6.75" x 4.50")
Thermostat guard: F29-0198
Room sensor (1 pack): RS01-SG
Thermostat Common Wire Kit: SA11

*The Sensi thermostat provides automatic dual fuel control without an outdoor sensor. A fossil fuel kit may be added if user selectable balance point settings are desired.

RATED DIFFERENTIALS (@ 6°F / HR)

	FAST	MED	SLOW
Heat (conventional gas/oil/elect):	0.5°F	0.75°F	1.9°F
Cool (central air):	0.9°F	1.2°F	1.7°F
Heat pump (heat and cool):	0.9°F	1.2°F	1.7°F
Heat pump (aux):	0.5°F	0.75°F	1.9°F

COMPATIBILITY

System Type	Compatible
Conventional heating and cooling	Gas furnace Air conditioner Electric furnace Boiler
Heat only	Gas furnace Electric furnace Boiler
Cool only	Air conditioner
Heat pump	

All systems require a common wire (c-wire)

SENSI ALERT

High temperature:
Low temperature:
High humidity:
Loss of heat/cool:

TRIGGER

Above 99°F
Below 45°F
Above 70%
Temp goes up or down 5°F during cycle

WIRELESS TECHNOLOGY

2.4 Ghz or 5Ghz Wi-Fi (802.11 a/b/g/n supported)
Bluetooth Low Energy

DIMENSIONS

5.6" W x 3.25" H x .77" D

STORAGE

-20° to 150°F (-29° to 65°C)
0%-90% RH non-condensing

OPERATING AMBIENT

32°F to +105°F (0°C to +41°C)

HUMIDITY RANGE

90% non-condensing max

DISPLAY TEMPERATURE RANGE

32°F to +99°F (0°C to 37°C)

TITLE 24 COMPLIANT

ENERGY STAR CERTIFIED

MODEL NUMBER	PROGRAMS		STAGES BY SYSTEM			SYSTEM TYPE	APPLICATIONS							POWER SOURCE	SELECTABLE PERFORMANCE FEATURES							
	Program Options	Periods Per Day Options	Single Stage Heat/Cool	Multi-Stage Heat/Cool	Heat Pump Heat/Cool	Universal, Single Stage, Multi-Stage, Heat Pump*	Gas / Oil / Electric	3 Wire Zone Valve	Millivolt Compatible	Economizer	Humidity Control (H)-Humidity / (D)-Dehumidify	Accessory Terminal	Dual Fuel Heat, Pump Control, Logic (L), Outdoor (O)	Remote Sensor Options, Indoor (I), Outdoor (O)	Battery (B), Hardwire / Common (H), Power Sharing (PS)	Auto Changeover	Programmable Fan (PF), Circulating Fan (CC)	Filter Change Reminder	Energy Mgt. Recovery / Early Start	Total Keypad Lockout (T), Partial Keypad Lockout (P)	Set-Point Temperature Limits Adjustable Min/Max	Display Size, Backlight with Key Press (K), Continuous Backlight with Common (C)
1F96U-42WF 1F96U-42WFB	7, NP, Geofencing	8 Max	1/1	2/2	4/2	✓	✓	✓	-	-	H, D	✓	L/O	I	H	✓	CC	✓	✓	T	✓	4.3" Color

TERMINAL DESIGNATIONS



#Thermostat has internal jumper on RC and RH. On two transformer systems, clip jumper wire on thermostat.

* Universal thermostats provide the flexibility to control Single Stage, Multi-Stage, or Heat Pump systems.